

Certificate



for European Product Safety

Reference No. 308886

Floor heating system

Type designation devimat DSVF-100, devimat DSVF-150

Certificate holder **DEVI A/S**
Ulvehavevej 61
DK-7100 Vejle
DENMARK

The product complies with the standard(s) EN 60335-2-96:2002
EN 60335-1:2002
IEC 60335-2-96:2002+A1:2003

Date of expiry 21 November 2008

LVD Information The products satisfy the provisions for CE marking according to the Low Voltage Directive 73/23/EEC and 93/68/EEC.

Terms in Intertek Semko's Agreement on certification. Additional information in Appendix.

Certification Body Intertek Semko AB, Product Certification *Place* Kista - Stockholm

Signed


Erik Wallerfelt

Date 21 November 2003



Appendix

Reference No. 308886

Technical data

Type designation / Typbeteckning devimat DSVF-100
Rated Voltage (V) / Märkspänning 230
Rated Power (W) / Märkeffekt 50-1000
IP-Class / IP-Klass X7
BRAND Name: DEVI alt. Danfoss
Product information /
Produktinformation 100W/m²

Type designation / Typbeteckning devimat DSVF-150
Rated Voltage (V) / Märkspänning 230
Rated Power (W) / Märkeffekt 75-1500
IP-Class / IP-Klass X7
BRAND Name: DEVI alt. Danfoss
Product information /
Produktinformation 150W/m²

Manufacturing site(s) DEVI A/S
Ulvehavevej 61
DK-7100 Vejle
DENMARK

Safety relevant parts in the user instructions shall be written in a language acceptable to the country where the product is to be used.

This certificate, which includes production control, is considered to constitute sufficient support for an EC Declaration of Conformity and CE marking of the products according to the Low Voltage Directive 73/23/EEC and 93/68/EEC.

Replaces previously issued Appendix dated 21 November 2003.

Kista/Stockholm
6 October 2005


Erik Wallerfelt



Intertek Semko AB

Torshamnsgatan 43, Box 1103, SE-164 22 Kista, Sweden
Telephone +46 8 750 00 00, Fax +46 8 750 60 30, www.sweden.intertek-etlsemko.com
Registered in Sweden: No SE556024059901, Registered office: As address



Appendix

Reference No. 308886

Length (m)	Area (m ²)	Input power type DSVF-100 (W)	Input power type DSVF-150 (W)
1	0,5	50	75
2	1	100	150
3	1,5	150	225
4	2	200	300
5	2,5	250	375
6	3	300	450
7	3,5	350	525
8	4	400	600
10	5	500	750
12	6	600	900
14	7	700	1050
16	8	800	1200
18	9	900	1350
20	10	1000	1500



Intertek Semko AB

Torshamnsgatan 43, Box 1103, SE-164 22 Kista, Sweden
 Telephone +46 8 750 00 00, Fax +46 8 750 60 30, www.sweden.intertek-etlsemko.com
 Registered in Sweden: No SE556024059901, Registered office: As address