



DEVIdry™ Kit 55

The DEVIdry™ Plug Kit is used to control the DEVIdry™ floor heating system designed for floor heating in dry rooms under wooden floorings, parquets, laminates and carpets.

The kit consists of the thermostat, the Circuit Device, the NTC Floor Sensor, the Supply Cord, the Power Supply Cord, The Connection Tool and aluminium Tape.

Benefits:

- All-in-the-box
- Easy installation
- Built-in 10A fuse
- Plug

Standard compliance:

- EN/IEC 60335-106 (with DEVIdry™)

Type	DEVIdry™ Plug Thermostat	DEVIdry™ CD, Circuit Device
Operation voltage	220V - 240 V	220V - 240 V
Standby power consumption	Max. 0,3 W	-
Relay:		
Resistive load	"No switching"	10A / 2300W @ 230 V
Sensing unit		NTC 15 kOhm at 25°C, 3 m
Regulation	n/a	±1 °C
Ambient temperature	0 °C to 45 °C	0 °C to 45 °C
Frost protection	5 °C	5 °C
Storage temperature	-20 °C to 55 °C	-20 °C to 60 °C
Ball pressure test temperature	75 °C	75 °C
Pollution degree	2 (Domestic use)	2 (Domestic use)
Controller type	1 C	-
Software class	A	A
Temp. display and setting unit	1°C. / step	n/a
IP class	30	30
Transmission frequency	868,199 - 869,999 mHz	868,199 - 869,999 mHz
Weight	390 g	390 g
Dimensions	78 x 120 x 30 mm	92 x 85 x 40 mm

Types

Item no.	Product name	Type	Temperature range	EAN no.
19911000	DEVIdry™ Plug Kit	55W	5 °C to 30 °C	5703466177914

Accessories

Item no.	Product name	Type	EAN no.
19911100	DEVIdry™ CD, Circuit Device	Relay Box, 10 A	5703466177938

Output	Subfloor		Top floor		
	Wood	Concrete	Wood	Laminate	Carpet
55 W/m ²	+	+	+	+	+

Note: Using a laminate top floor requires a minimum thickness / quality of 10 mm HDF (>800 kg / m³).

The DEVIdry™ Kit 55 is supplied with an EU Schuko mains plug.