



Installation Guide

DEVILink™ RS

Room Sensor

www.DEVI.com

DEVI® 

DEVlink™ RS is a battery operated **room device**. It measures the ambient room temperature and allows you to control heating



IP21



Avoid direct sunlight to DEVlink™ RS




Mount in height of 80-150 cm



Mount max. 5 to 6m from *living connect*®



Mount at least 50 cm from windows/doors that will be left open occasionally



Turn the device around




Remove the back panel by gently pressing your thumbs on the panel and pull downwards



Fix the back panel to the wall












Install the front panel by gently letting it slide on the back panel again



Tamper-proof, locked

Adding DEVlink™ RS to a system is made from the DEVlink™ CC. For further information, see separate instruction.



Display information	
	Ambient temperature
	Floor temperature
Short green flash	Not included in network
Green fast flash	Inclusion in progress
Red flash +  for 5 seconds	Inclusion failed
 ON	Link test in progress
Red flash +  for 5 seconds	Link test failed
 ON + Red LED flash every 2½ min.	Low battery level
 ON + Red LED flash every 30 seconds	Critical battery level
E5	Floor sensor short circuited
E6	Floor sensor lost
 ON	Tamper-proof enabled by DEVllink™ CC
 Flash	Limited by DEVllink™ CC

Technical specifications	
Battery	Alkaline 2 x AA, 1.5 V
Battery lifetime	Up to 4-5 years
Backlight	Green LED
Ambient temperature	0 to +40 °C
Battery monitoring	The sensor has a built-in monitoring circuit, which will detect low or critical battery level
Transmission frequency	868.42 MHz
Transmission range in normal buildings	Up to 30 m
Transmission power	Max. 1 mW
IP class	21
Dimensions (mm)	75 x 75 x 24

Radio Equipment Directive

SIMPLIFIED EU DECLARATION OF CONFORMITY

Hereby, Danfoss A/S declares that the radio equipment type DEVlink™ RS is in compliance with Directive 2014/53/EU

The full text of the EU declaration of conformity is available at the following internet address: **devi.danfoss.com**



Danfoss A/S
Electric Heating Systems
Ulvehavevej 61
7100 Vejle
Denmark

Phone: +45 7488 8500
Fax: +45 7488 8501
E-mail: info@DEVI.com
Web: www.DEVI.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. DEVI and the DEVI logo-type are trademarks of Danfoss A/S. All rights reserved
