

No. P07208089

Accredited Certificate (ref. NA-PROD 001)

Order No.

88836

Applicant	Danfoss A/S Industri Service Global Approvals Nordborgvej 81, Office E14-S4a, DK-6430 Nordborg, Denmark
Manufacturer	DEVI A/S Ulvehavevej 61 DK-7100 Vejle Denmark
Factory	DEVI A/S Bødkervej 8 DK-7100 Vejle Denmark
Trade mark	DEVI
Product	Thermostat
Model/type	DP-10
Rating	Max 32A, 180-250VAC / 18-26VDC 50/60Hz, Max 3W
Principal characteristics	Electronic thermostat, micro disconnection, type 1.B, Class II, Category D, normal situations, -10T40, PTI 175, pillar terminals, IP20, for DIN rail mounting
Standard(s)	Safety std.: EN 60730-1:2000; A1; A12; A13; A14 and EN 60730-2-7:91 + A1:97 + A11;A12;A13 EN 60730-2-9:2002; A1; A2; A11; A12 including possible listed national conditions/deviations for Norway.  EMC std.: EN 60730-2-9:2002; A1; A2; A11; A12
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemko's name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.
Additional information	This certificate replaces previously certificate dated 2007-12-04 due to correction in standards listed. Additional information on page 2
Variants	This Certificate also covers variants with Position No. 001 See next page

Date of issue 11 December 2007



signature

Geir Hørthe

Certification Department

No. P07208089

Accredited Certificate (ref. NA-PROD 001)

Order No.

88836

## Additional Information:

The abovementioned certified equipment complies with current regulatory requirements regarding electrical safety and electromagnetic compatibility (EMC) in Norway and other EU/EEA member states.

## Product

Thermostat

## Trade mark

Danfoss

## Position No

001

## Model/type

D850

## Rating and principal characteristics

Max 32 A Max 3 W 180-250VAC 18-26 VDC 50/60 Hz

## Additional information

Electronic thermostat, micro disconnection, type 1.B, Class II, Category D, normal situations, -10T40, PTI 175, pillar terminals, IP20, for DIN rail mounting

Date of issue 11 December 2007



signature

Geir Hørthe

Certification Department

## NOTIFICATION

We hereby confirm that the product(s) appearing from the certificate with the above certificate reference also comply(ies) with requirements for secondary certification in the following Nordic country(ies):

Denmark, Finland, Sweden

Applicant for Denmark	Danfoss A/S Industri Service Global Approvals Nordborgvej 81, Office E14-S4a, DK-6430 Nordborg, Denmark Att. Gilbert Jessen
Applicant for Finland	Danfoss A/S Industri Service Global Approvals Nordborgvej 81, Office E14-S4a, DK-6430 Nordborg, Denmark Att. Gilbert Jessen
Applicant for Sweden	Danfoss A/S Industri Service Global Approvals Nordborgvej 81, Office E14-S4a, DK-6430 Nordborg, Denmark Att. Gilbert Jessen
Safety standard(s) applied	Confer the attached certificate.
EMKO TS document(s) considered	Not applicable
EMC/RFI requirements	Confer the attached certificate.
The assignment is based on	Testing in own premises.
Limitations or reservations regarding the performed testing/examination	None
Certification marks	Affixing of the certification mark(s) of other Nordic body(ies) on the products must not take place before notice about national certification is received from the individual body.
Production surveillance	Will be carried out by Nemko according to agreed procedures.
Other information	Copy of the certificate, this Notification and other agreed documentation are transferred directly from Nemko to DEMKO, FIMKO, SEMKO
Test sample(s) must be submitted to the secondary body(ies)	No

This Notification may be challenged if it is more than 3 years old.

Date of issue 04 December 2007



signature

Geir Hørthe

Certification Department